



### Sealing Sheet Pile Interlocks (Ball and Socket Type) PZ27

**Adeka Ultraseal® A-30** is an effective and efficient way to seal sheet pile interlocks prior to driving piles.


1. Threaded pile showing interlock gap (Approximately 3/8")



2. Socket with 1/4" cured A-30. **EASY APPLICATION:** Clean interlocks - level piles with socket exposed (set pile on edge - see photo) - fill socket with A-30 approximate 1/4" depth at center. One gallon will cover approximately 70'. Allow A-30 to cure. Drive piles with ball side leading.



3. Threaded piles with cured A-30 in the interlock.



**OCM, Inc.**

1120 Peterson Road, Grayslake, IL 60030

Toll Free: 866-457-5710 • Phone: 847-462-4258 • FAX: 847-462-4259

www.adeka.com • www.ocm-inc.com • sales@ocm-inc.com